

PAINT FINISH ASSORTMENT

Beginner set for the professional processing of painted surfaces.



Designation	Art. No.	P. Qty.
Paint Finish Assortment*	0964 893 8	1

Areas of application:

For the professional processing of paint mist, paint transitions, and defective points in freshly painted or hardened top coats. Vehicle detailing. Surface refinement.

Application:

Shake polish well before using. Apply a few drops of the polish to the polishing pad and a small amount to the object to be treated. Apply the polishing pad to the object and spread it manually onto the surface to be polished. After that, start the polishing machine and, applying soft pressure at 1500 – 2000 rpm, process the surface with even movements until the desired result has been achieved.

Note:

With a dry polishing pad, apply a little more polish. Remove the polish residue with a microfiber cloth. Proceed in sections.

- ▶ Innovative polishes on the basis of aluminum oxide.

Your advantage:

- Outstanding removal power.
- Very fast processing of defective points.
- High gloss level.
- Can be used universally on all commercial top-coat paint systems.

- ▶ Newest polish generation.

Your advantage:

- Work with state-of-the-art technology.

- ▶ Assortment

Your advantage:

- Best suited for mobile use.

* Contents:

2 professional vehicle polishes (P10 + P30)
250 abrasive polishing plates (Velcro) P2000 used for the removal of dust inclusions and fine surface defects.

Sanding block set (sanding block, soft interface, abrasive polishing plate moistener)

5 automotive fine-sanding disks P2000 for matt-finishing the surface

2 "Orange" sanding pads, dia. 85 mm

1 "Blue" sanding pad, dia. 85 mm

Pneumatic polishing machine with speed control.

Adhesive plate (Velcro), dia. 75 mm

- ! **Adhesive plate (Velcro)**
dia. 50 mm/dia. 75 mm
Art. No. 0586 585 050/075
P. Qty. 1
- Sanding pad dia. 85 mm**
Art. No. 0585
P. Qty. 5
- P10 Quick Sanding Polish Plus**
Art. No. 0893 150 010
P. Qty. 1/5
- P30 Anti-Hologram Polish Plus**
Art. No. 0893 150 030
P. Qty. 1/5
- Polishing plates (Velcro), P2000**
Art. No. 0558 200 0
P. Qty. 250

This information is only a recommendation based on our experience. Preliminary testing required!
For further information, see the technical information leaflet.